

# ECS setting the standards in pressroom solutions

## Plate Care Range

05/08/2013

Listed below are examples of our most commonly used plate maintenance chemical portfolio covering the majority of plate requirements. We also offer bespoke products where appropriate.

### PLATE CLEANERS

Product	Description
<i>C200 GP Plate Cleaner</i>	Everyday general purpose plate cleaner. Acidic emulsion of cleaning and desensitizing agents.
<i>C201 HD Plate Cleaner</i>	Stronger cleaning action to C200 with mild abrasive action.
<i>C270 Ultra Plate Cleaner</i>	Strongest cleaner on the range –high in solvency and abrasive power for increased de-sensitizing and scratch repair.
<i>C214 UV Plate cleaner</i>	High strength cleaner most suited to robust baked positive plates using UV inks.
<i>C280 All Purpose Plate Cleaner</i>	Suitable for all plate types with strong cleaning and mild abrasive action.
<i>C266 Quickmaster plate cleaner</i>	Suitable for various digital waterless plates and can also be used for many flexographic plates.
<i>C246 Poly Plate Cleaner</i>	Manual cleaning chemical for polyester plates as used in flexography. Suitable for all ink types.

### MISCELLANEOUS PLATE CHEMICALS

Product	Description
<i>C205 Plate Etch</i>	acid etch solution.
<i>C238 Strong Plate Etch</i>	stronger version of C205
<i>C203 Gum Arabic</i>	Made from naturally occurring acacia gum.
<i>C237 DP Washout Gum</i>	Used as a mild cleaner and can be used to store plates overnight.
<i>C225 Gum double strength</i>	high viscosity gum Arabic solution for export markets that can use it neat or dilute it before use.
<i>C206 Auto plate wash</i>	specialist automatic plate wash emulsion.
<i>C240 Plate Scratch Remover</i>	New solution for repairing and desensitizing scratches on plates.
<i>DM320 Positive Developer 1:6</i>	Concentrated positive plate developer solution.
<i>DM405 High Strength Negative Developer</i>	For Negative working plates. High strength for increase developing power.
<i>C251 Thermal Plate Developer</i>	Ready to use developer for CTP plate technology.
<i>C252 CTP Plate Replenisher</i>	Replenisher for CTP plate processing. To be used along with C251